



# 941 – adding elegance and improved visibility to the low level environment

## 941 Step Light LED

The Gardco 941L recessed steplights are architecturally styled luminaires precisely constructed of die cast aluminum, providing light with high performance, long life LED systems. Retrofit kits are also available, making it possible to update installations of classic 941 Gardco fluorescent and HID step lights to LED without the need to replace the back housing. A field adjustable junction box enhances design flexibility. Self-compensating silicone gasketing completely excludes moisture, insects and contaminants. A choice of two (2) architecturally designed faceplates allows for a variety of applications.

### Benefits

- Uses up to 50% less energy than HID and fluorescent alternatives
- Provides added corrosion resistance
- Low-glare illumination
- Quick installation and maintenance
- Eliminates potential for misapplication

### Features

- Utilizes an advanced high output LED array
- Sealed and gasketed
- TGIC polyester powdercoat finish
- Available for installation in all types of wall construction

### Application

- Walkways

## 941 Step Light LED

### Versions

