



942 - adding elegance and improved visibility to the low level environment

942 Step Light LED

The Gardco 942L recessed aisle lights are architecturally styled luminaires precisely constructed of die cast aluminum, providing light with high performance, long life LED systems. Retrofit kits are also available, making it possible to update installations of classic 942 Gardco fluorescent and HID step lights to LED without the need to replace the back housing. A field adjustable junction box enhances design flexibility. Self-compensating silicone gasketing completely excludes moisture, insects and contaminants. A choice of three (3) architecturally designed faceplates allows for a variety of applications.

Benefits

- Uses up to 50% less energy than HID and fluorescent alternatives
- Provides added corrosion resistance
- Low-glare illumination
- Quick installation and maintenance
- Eliminates potential for misapplication

Features

- Utilizes an advanced high output LED array
- Sealed and gasketed
- TGIC polyester powdercoat finish
- Available for installation in all types of wall construction

Application

- Walkways

942 Step Light LED

Versions

