



Aktra - heavy-duty floodlighting for hard to light spaces

Aktra Floodlight

Aktra 1000 floodlight luminaire features low-profile, heavy-duty housing that is suitable for a variety of floodlighting applications. AF1000 achieves precise cutoff to control glare and restrict spill light, and meets IES criteria for Cutoff distribution. A secondary element reflects high angle rays back into the beam to achieve a high beam. Housing is constructed of permanent mold aluminum alloy with integrally cast heat dissipating fins. Standard unit constructed to IP65. Marine listing unit available (MAF) constructed to IP66. ETL/cETL listed to the UL 1598 standard, suitable for Wet Locations. UL 1598A Marine Listing available.

Benefits

- Superior durability
- Controls glare and unwanted spill light
- Maximized efficiency

Features

- Heavy-duty housing
- Precise cutoff
- Secondary high-angle reflector

Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways
- Road and Street