



# Clean architectural design

## Alcyon LED Horizontal II

Architecturally styled Alcyon LED Cylinders offer excellent beam control and aesthetics while providing high performance accent lighting for retail and commercial applications.

### Benefits

- Designed around the finest white LEDs
- Thermally engineered for superior optical performance
- Available in a range of beam spreads for lighting flexibility and is dimmable

### Features

- Field changeable optics
- Vertical and horizontal locking preserves original lighting design intent
- Aiming indicator allows a series of luminaires to be precisely set to the same aiming angle
- Lumens: 600 and 1000

### Application

- Fashion
- Food and Large Retailers

## Alcyon LED Horizontal II

### Versions

