



# Clean, elegant architectural styling

## Alcyon Low Voltage

Alcyon Low and Line Voltage luminaires utilize today's reliable and economical halogen and Incandescent lamps for ambient, task, accent and wall washing applications. Available in PAR20, PAR30, PAR38 and T4 halogen sources, Alcyon delivers bright light that is easily dimmable.

### Benefits

- Infinite horizontal rotation for maximum aiming flexibility without "dead spots"
- Lamp-forward design improves access and simplifies relamping
- Captive accessory cartridge accepts two accessories and provides excellent glare control

### Features

- The silent electronic transformer includes short-circuit and over-heat protection
- Die cast aluminum construction throughout with a durable baked enamel finish
- Available in MR16 and T4 2-pin lamping

### Application

- Fashion
- Food and Large Retailers

## Alcyon Low Voltage

### Versions

