



# Modern rustic design built to perform

## Ancestra LED post top (AT10-AT20-AT30-AT40)

Its eye-catching design will set your project apart. The Lumec Ancestra LED post top and pendant luminaires present a new twist on an old-fashioned design. By combining the best aspects of past and present forms with the best that modern technology has to offer, the Ancestra luminaires epitomize Lumec's design philosophy beautifully: to combine the best technology with an elegant design. Equipped with an optional copper cupola, a decorative cage, and crown accents, the result is a luminaire that complements any project with rustic flair and modern appeal without sacrificing photometric quality.

### Benefits

- Versatile luminaires available with various style options
- Post top and pendant versions available to suit a wide range of applications
- Highly efficient IP66 optics are protected from the elements and ensure optimal photometric performance
- Maximizes energy savings with multiple driver options and programmed dimming options

### Features

- Multiple lumen packages with output of up to 7,853 lumens
- Type 2, 3, 4, and 5 optics available
- 4000K and 3000K color temperatures available
- Dimming driver standard

### Application

- Municipal Buildings
- Parks and Plazas
- Road and Street

## Ancestra LED post top (AT10-AT20-AT30-AT40)

### Versions

