



APX LED – Durability and high performance

APX LED High Bay

The APX LED High Bay provides durability and high performance for your customer's demanding environments. The APX can be specified for many areas requiring a sealed luminaire, such as laboratories, food processing, parking areas, and other industrial applications. The rugged housing and clear or frosted lens options combine for durable and effective lighting that is also comfortable for the occupants. LED technology provides efficiency, long life, and reduces energy costs.

Benefits

- Designed to resist corrosion
- Easy installation and maintenance

Features

- Sealed luminaire
- Injection molded, high impact clear acrylic lens is standard
- Tamper-resistant, stainless steel, captive latches
- Suitable for wet locations

Application

- Manufacturing
- Education
- Cleanrooms
- Food Processing

APX LED High Bay

Versions

