



Stylish with clean lines

Arioso Recessed

Arioso Recessed offers simple clean lines in combination with soft natural illumination. This series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, Arioso Recessed provides a soft unassuming glow with comfortable illumination.

Benefits

- Architectural recessed direct/indirect lighting for glare free illumination
- Suitable for row mounting

Features

- Soft white baked enamel finish
- Fully recessed mounting
- UL listed for damp locations
- Swing down lamp shield for easy relamping

Application

- Office
- Banks
- Hospitality
- Fashion

Ariosso Recessed

Versions

