



# Stylish with clean lines

## Arioso Recessed Shallow

The Day-Brite / CFI Arioso Recessed Shallow is ideal for shallow ceiling applications and offers simple clean lines in combination with soft natural illumination. With micro-perforated baskets and contoured seamless reflectors, this series focuses on providing smooth comfortable lighting while subtly complementing the space. Flexible enough to integrate with any architectural design, these luminaires provide a soft unassuming glow with comfortable illumination to optimize work and recreational activities.

### Benefits

- Architectural recessed direct/indirect lighting for glare free illumination
- Suitable for row mounting
- Great for shallow plenum applications

### Features

- Shallow housing requires only 3-5/8 of plenum space
- Fully recessed mounting
- UL listed for damp locations
- Swing down lamp shield for easy relamping

### Application

- Office
- Banks
- Hospitality
- Fashion

## Arioso Recessed Shallow

### Versions

