



TFHAM4 – providing additional mounting flexibility

Arms, Pendant Adapter with Finial (TFHAM4)

2-3/8" O.D. horizontal arm mounting adapter without photocell twist-lock receptacle

Benefits

- Superior weatherability
- Fade and abrasion resistant
- Quick and easy field installation

Features

- Low copper, cast aluminum construction
- Polyester powdercoat finish

Application

- Road and Street
- Bridges, Monuments, Facades

Arms, Pendant Adapter with Finial (TFHAM4)

Versions

