



Providing additional mounting flexibility

Bracket Arm Adapters

The Hadco TFHAM3 and TFHAM4 are 2-3/8" O.D. horizontal bracket arm mounting adapters with a decorative finial (TFHAM4) or photocell twist-lock receptacle (TFHAM3). The TFTC1 adapter is typically used for retrofit applications when there is an installed bracket arm that is vertically threaded.

Benefits

- Superior weatherability
- Fade and abrasion resistant
- Quick and easy field installation

Features

- Low copper, cast aluminum construction
- Polyester powdercoat finish

Application

- Road and Street
- Bridges, Monuments, Facades

Bracket Arm Adapters

Versions

