



BL16 – showcasing the best features of your landscape

BL16 Micro Accent

Hadco's BL16 is a low voltage brass bullet used for accent lighting. It's made from die cast brass and has a fully rotatable shroud with gasket. Optics include a clear tempered glass affixed at 10° angle for natural cleaning with a 50W maximum MR16 bi-pin lamp. Also available with a Philips MR16 LED lamp

Benefits

- Design flexibility
- Able to direct light with ultimate precision
- Offers 25,000 hour life with LED
- Quick and easy installation

Features

- Available with conventional and LED technology
- Available in a variety of finishes
- Fully-adjustable swivel arm with vibration-proof locking teeth
- Pre-wired

Application

- Landscape

BL16 Micro Accent

Versions

