



# BL5016 - showcasing the best features of your landscape

## BL5016 Micro Accent

The housing is constructed of double gasketed, die cast marine-grade alloy aluminum for long life. With vibration-proof serrated teeth along with the base of the housing, it provides a positive lock. A 360 degree fully adjustable swivel arm allows for precise lighting along with an angled lens for self-cleaning. The fixture is UL, cUL listed for a 50 watt MR16 lamp. also available with a Philips MR16 LED lamp. The socket features a retention clip to secure the lamp in place.

### Benefits

- Ensures long-lasting durability
- Able to direct light with ultimate precision
- Offers up to 25,000 hour life with LED
- Provides added corrosion resistance
- Quick and easy installation

### Features

- Die-cast marine grade aluminum alloy housing
- Fully-adjustable swivel arm with vibration-proof locking teeth
- Available with warm or cool LEDs
- Thermoset powdercoat finish
- Pre-wired

### Application

- Landscape

## BL5016 Micro Accent

### Versions

