



# BM – adding a touch of originality to any project

## Bracket (BM)

The BM mounting arm features a 2 3/8" O.D. (60 mm) extruded-aluminum tube bent at 180° welded to a cast-aluminum adaptor. The mounting arm includes an aluminum decorative element welded to the arm. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\\_en.php" target="\\_blank"~GT~](http://www.lumec.com/Lumec3Dv2/home/index_en.php)~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 2.00

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (BM)

### Versions

