



CRA - adding a touch of originality to any project

Bracket (CRA)

The CRA mounting arm features a seamless 1" x 2" (25 x 51 mm) rectangular extruded aluminum tube and cast decorative scroll, welded to a cast-aluminum plate. The mounting arm is equipped with a 4" round (102 mm) by 4" high (102 mm) tenon for luminaire mounting. The CRA plate is mechanically fastened using stainless steel hardware to a central pole adaptor slip-fitting 9" (229 mm) over a 4" (102 mm) O.D. pole or tenon. ~LT~[a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php)
target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 1.40

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (CRA)

Versions

