



# CRH - adding a touch of originality to any project

## Bracket (CRH)

The CRH mounting arm features one 2 3/8" round (60 mm) extruded-aluminum arm welded to the central pole adaptor. Both are closed by a decorative castaluminum cover. The mounting arm includes two decorative rolled sections of aluminum rods welded between the arm and the central pole adaptor. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The central pole adaptor slip-fits 12" (305 mm) into a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\\_en.php" target="\\_blank"~GT~](http://www.lumec.com/Lumec3Dv2/home/index_en.php)~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 1.95

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (CRH)

### Versions

