



M20A – adding a touch of originality to any project

Bracket (M20A)

The M20A mounting arm features a 2 7/8" round (73 mm) double-bend extruded-aluminum tube, welded to a cast-aluminum clamp-on pole adaptor. Comes with a standard decorative pole cap. The mounting arm includes a flat bent aluminum decorative element mechanically secured to the arm and pole. A suspended luminaire adaptor is mechanically secured to the arm by a decorative cast-aluminum clamp and stainless steel hardware. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The mounting arm clamp is mechanically assembled on a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) pole using stainless steel hardware. The location is pre-drilled on Lumec poles. ~LT~http://www.lumec.com/Lumec3Dv2/home/index_en.php target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Decorative, yet durable
- Clamp-on

Features

- Available in a variety of mounting configurations
- EPA of 2.06
- Decorative pole cap included

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (M20A)

Versions

