



MJ - adding a touch of originality to any project

Bracket (MJ)

The MJ mounting arm features a 2 3/8"-O.D. (60 mm) extruded-aluminum tube bent at a 180° angle welded to a cast-aluminum pole-top adaptor. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. ~GT~ The MJ bracket is offered with LG option (medaillon to accept logo) ~LT~http://www.lumec.com/Lumec3Dv3/home/index_en.php target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 2.00

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (MJ)

Versions

