



# MR - adding a touch of originality to any project

## Bracket (MR)

The MR mounting arm features a 2 3/8" round (60 mm) extruded-aluminum arm welded to an aluminum central pole adaptor. The mounting includes a decorative bent extruded-aluminum tube welded to the central pole adaptor and to the arm. The cast-aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. ~LT~[www.lumec.com/Lumec3Dv2/home/index\\_en.php](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 2.10

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (MR)

### Versions

