



# PC - adding a touch of originality to any project

## Bracket (PC)

The PC mounting arm features a 2 3/8" (60 mm) round extruded-aluminum arm welded to the central pole adaptor. The mounting arm includes an extruded-aluminum decorative rod welded to the central pole adaptor and to the arm. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. ~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index\_en.php" target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 2.35

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (PC)

### Versions

