



# PM - adding a touch of originality to any project

## Bracket (PM)

The PM mounting arm features a 2 3/8" O.D. (60 mm) extruded-aluminum tubing bent at a 90° angle and welded to two 1" (25 mm) extruded-aluminum arms, two decorative rings. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The central pole adaptor slip-fits 12" (305 mm) into a 4" (102 mm), 5" (127 mm) or 59/16" (141 mm) O.D. pole or tenon. ~LT~br~GT~ ~GT~ The PM is available with the OV option that can accommodate up to two 175W ballasts.~LT~br~GT~ ~GT~ For pole supplied by others, we strongly recommend the OV option.~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\_en.php" target="\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

### Benefits

- Decorative, yet durable

### Features

- Available in a variety of mounting configurations
- EPA of 2.53

### Application

- Bridges, Monuments, Facades
- Road and Street

## Bracket (PM)

### Versions

