



RSAR - superior strength

Bracket (RSAR)

- Made of cast A356 aluminum, mechanically assembled to the pole.
 - Available for a 4" (102mm) to 4.9" (124mm) or 5" (127mm) to 6" (152mm) round or 4" (102mm) minimum square pole.
 - Available with RoadStar Only.
 - Consult Factory to insure compatibility with your pole and fixture.
- [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php" target="_blank"~GT~](http://www.lumec.com/Lumec3Dv2/home/index_en.php)
~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~

Benefits

- Ensures lasting durability

Features

- Cast aluminum construction
- Fits round and square poles of various sizes
- Available with RoadStar luminaires

Application

- Road and Street