



TM - adding a touch of originality to any project

Bracket (TM)

The TM mounting arm features a 2 3/8" O.D. (60 mm) extruded-aluminum tube bent at 180° and welded to a pole adaptor. The mounting arm includes an extruded-aluminum 1 1/16" (27 mm) O.D. decorative element welded to the arm. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The aluminum central pole adaptor slip-fits over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole. ~LT~[a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 2.27

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (TM)

Versions

