



UM - adding a touch of originality to any project

Bracket (UM)

The UM mounting arm features a 2 3/8" round (60 mm) extruded-aluminum arm welded to an aluminum central pole adaptor. The mounting arm includes two cast-aluminum decorative elements welded to the central pole adaptor and to the arm. The luminaire adaptor will accept a luminaire equipped with Lumec's four-bolt mounting system. The central pole adaptor slip-fits 12" (305 mm) into a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. ~LT~br~GT~ ~GT~ The UM is available with the OV option that can accommodate up to two 175W ballasts. ~LT~br~GT~ ~GT~ For pole supplied by others, we strongly recommend the OV option. ~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php" target="_blank"~GT~ ~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~ ~LT~/a~GT~

Benefits

- Decorative, yet durable

Features

- Available in a variety of mounting configurations
- EPA of 2.33

Application

- Bridges, Monuments, Facades
- Road and Street

Bracket (UM)

Versions

