



# AR4/AR6/AR8 – adding a touch of originality to any project

## Brackets (AR4/AR6/AR8)

The AR4 / AR6 / AR8 mounting arms a tapered spun aluminum arm of 4" by 2 7/8" (102 by 73 mm) to 2 3/8" (60 mm) O.D. at the luminaire end, mechanically assembled to the central housing. The mounting arms include a decorative bent piece of aluminum, mechanically assembled to the pole and to the arm using stainless steel hardware, complete with a decorative cast aluminum cap on each end. The central pole adaptor is complete with a decorative cast-aluminum cap. With the IA configuration a cast-aluminum decorative side cap is added. The central pole adaptor slip-fits 9" (229 mm) over a 4" (102 mm), 5" (127 mm) or 5 9/16" (141 mm) O.D. pole or tenon. ~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\_en.php" target="\_blank"~GT~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~LT~/a~GT~

### Benefits

- Decorative, yet durable
- Extended reach

### Features

- Available in a variety of mounting configurations

### Application

- Bridges, Monuments, Facades
- Road and Street

## Brackets (AR4/AR6/AR8)

### Versions

