



CRM4/CRM6/CRM8 – adding a touch of originality to any project

Brackets (CRM4/CRM6/CRM8)

The CRM4 / CRM6 / CRM8 mounting arms feature a 2 3/8" O.D. (60 mm) doublebend steel tube welded to a steel adaptor. The mounting arms assemblies include cast-aluminum decorative elements. The pole-top adaptor slip-fits 10 3/8" (264 mm) over a 2 7/8" (73 mm) O.D. tenon. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index_en.php"](http://www.lumec.com/Lumec3Dv2/home/index_en.php) target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Decorative, yet durable
- Extended reach

Features

- Available in a variety of mounting configurations

Application

- Bridges, Monuments, Facades
- Road and Street

Brackets (CRM4/CRM6/CRM8)

Versions

