



BUL16 – showcasing the best features of your landscape

BUL16 Micro Accent

The BUL16 is a low voltage composite Bullyte used for accent lighting and available with a 35 W maximum MR16 bi-pin lamp or a Philips MR16 LED lamp. Construction includes a one-piece injection moulded ULTEM® High Performance Polymer composite with fully rotatable shroud and a fully-adjustable swivel arm with vibration-proof locking teeth. Optics have a clear tempered glass affixed at 10° angle for natural cleaning.

Benefits

- Design flexibility
- Able to direct light with ultimate precision
- Offers 25 000 hour lifetime with LED
- Quick and easy installation

Features

- Available with conventional and LED technology
- Available in a variety of finishes
- Fully-adjustable swivel arm with vibration-proof locking teeth
- Pre-wired

Application

- Landscaping

BUL16 Micro Accent

Versions

