



Callisto - casting a timeless light on any project

Callisto Arm Mount (CALM)

Recognized for being visually appealing, they are also very technologically advanced. When creativity is focused on details, the details will create ambience. The soft light cast by these discrete luminaires with their refined design makes them an integral part of a finished work. Our wall sconces were designed to complement our lines of luminaires and to add a polished look and feel to any project. [~LT~a href="http://www.lumec.com/Lumec3Dv3/home/index_en.php"](http://www.lumec.com/Lumec3Dv3/home/index_en.php) target="_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~

Benefits

- Guarantees high quality and precise lighting
- Protects against dirt and debris
- Long-term photometric performance
- Minimizes light trespass
- Quick and easy maintenance

Features

- Die-cast acrylic globe with hydroformed and anodized reflector
- Unique design includes cage inside globe
- IP66 rated Smartseal optics
- Tool-free access to internal components
- Decorative refractor with integrated colored LED option

Application

- Bridges, Monuments, Facades
- Road and Street