



# Callisto - casting a timeless light on any project

## Callisto Post Top (CAL2)

Quality of production and attention to detail ensures its durability, even in the most challenging environments. Inspired by classical and contemporary elements, the Callisto's refined lines cast a timeless light on any project. The combination of two lighting technologies assures maximum light control while contributing to the spirit of a project's settings and preserving the dark skies. The Callisto is the perfect choice for those looking for sophistication, unique styling, and performance. [~LT~a href="http://www.lumec.com/Lumec3Dv2/home/index\\_en.php" target="\\_blank"~GT~~LT~b~GT~Lumec3D: Online 3D Configurator~LT~/b~GT~~LT~/a~GT~](http://www.lumec.com/Lumec3Dv2/home/index_en.php)

### Benefits

- Guarantees high quality and precise lighting
- Protects against dirt and debris
- Long-term photometric performance
- Minimizes light trespass
- Quick and easy maintenance

### Features

- Die-cast acrylic globe with hydroformed and anodized reflector
- Unique design includes cage inside globe
- IP66 rated Smartseal optics
- Tool-free access to internal components
- Decorative refractor with integrated colored LED option

### Application

- Bridges, Monuments, Facades
- Road and Street

## Callisto Post Top (CAL2)

### Versions

