



Unparalleled design

Canopy Kits

Basic Lytespan track can be mounted in a variety of surface or stem patterns, placed vertically or horizontally on walls, and be cut in the field. Basic track can also be used with Suspension Beam or Recessed Housings. Capacity is 20 amps at 120V per branch circuit. For straight runs, order one 2-foot, 4-foot or 8-foot Individual Track section and as many 8-foot Joiner sections as required including each straight run of track between intercepts.

Benefits

- For clean look when powering through junction box

Features

- Mounts to a 4" or 3" octagonal outlet box
- Mounts along runner or at the intersection of runners

Application

- Fashion
- Food and Large Retailers

Versions



6060BK