



# Specification grade and durable

## Caravel Vandal Resistant Wraparound

The specification grade Caravel Vandal Resistant Wraparound offers durable white metal end caps and a self-centering lens that is supported the entire length. The lens may be hinged from either side for easy maintenance.

### Benefits

- Lens withstands 7 ft-lbs impacts without breaking
- Luminaires can be bolted together in continuous row applications

### Features

- Housing and end plates are phosphate treated for maximum corrosion resistance
- 1% DR acrylic lens
- Knockouts in end plates
- UL listed for damp locations

### Application

- Manufacturing
- Office
- Banks
- Hospitality
- Security Lighting

## Caravel Vandal Resistant Wraparound

### Versions

