



Clean design. Functional form.

Gimbal Track Heads

Classic Gimbal Ring style Track Heads feature minimal, functional forms with cleanly detailed yoke and ring-shaped lamp holders for PAR20, PAR30, and PAR38 lamp sizes.

Benefits

- Designed with minimalistic form to create a close fit with LED lamps
- Units adjust horizontally up to 350° and vertically up to 90°
- Front re-lamping for easy maintenance
- Permanently-tensioned trunion mounting allows rings to remain fixed at any angle

Features

- Compatible with Lightolier Basic and Advent Track Systems. Adjustable brass contacts extends for connection to 2nd circuit in Advent Track
- Available in PAR 20/30/38 lamp sizes
- Available in white or black finishes

Application

- Fashion
- Food and Large Retailers

Gimbal Track Heads

Versions



9030NBK

