



Reliable and versatile

CMF/CNM Series Steel Emergency Unit

These emergency units provide reliable emergency lighting during power outages and other emergencies. The housing is constructed of 18 to 20 gauge steel and has the versatility of six conduit knockouts to customize lamp head configurations. See remote lamp head specification sheet CA-51500 for all available lamp heads.

Benefits

- Designed to be corrosion resistant
- Easily mounted

Features

- Chicago Approved
- New York City Approved
- UL listed for damp locations
- All models feature the Intelli-Charge self-diagnostic circuitry

Application

- Exit and Emergency

Versions

