



CRF Cleanroom - Superior and practical

CRF Series Recessed Cleanroom

The CRF Containment Series is designed to meet criteria for critical environments in recessed applications.

Benefits

- Designed to meet the criteria for critical environments

Features

- Suitable for wet locations
- Suitable for Class 100, 1,000 , 10,000, 100,000 environments
- Captive stainless steel Phillips flat head fasteners are standard

Application

- Laboratories
- Manufacturing
- Pharmaceuticals
- Medical

CRF Series Recessed Cleanroom

Versions

