



# Simple, easy, convenient

## Cubelite

Smooth opal or prismatic acrylic lens options offer diffused light. Ideal for corridor, stairwell or vanity applications.

### Benefits

- Multiple mounting option means flexibility for different needs

### Features

- Suitable for wall or ceiling mounted applications
- Available in lengths of 2', 3' or 4'
- Suitable for mounting on low density surfaces
- Only 4-13/16" deep

### Application

- Office
- Banks
- Hospitality
- Fashion
- Manufacturing

## Cubelite

### Versions

