



DB21 – durable versatility

DB21 Bollard

The DB Series is a line voltage Bollard available in incandescent, CFL, HID and LED sources. This versatile luminaire features a dome roof with die-cast aluminum louvers, and in a variety of heights. Optics include a symmetric, die-cast aluminum louvers with underside painted with highly reflective white powdercoat and a tempered glass globe. The LED sources features a 9.5W Philips LED EnduraLED lamp, LED 4Kv medium base porcelain socket A19. The 2700K warm white delivers 800 lumens and the lamp life is rated at 25,000 hours.

Benefits

- Ensures long-lasting durability
- Tightly sealed protection
- Highly weather-resistant
- 25,000 hour life with LEDs

Features

- Die-cast aluminum dome and louvers
- Clear molded glass lens
- CraftStone or polyester powdercoat finish
- Available with a variety of light sources, including LED

Application

- Walkway

DB21 Bollard

Versions

