



DCL Designer Cleanroom - Superior and practical

DCL Designer Cleanroom

The Designer Clean Room is a recessed luminaire tested to federal standard 209E and designed for use with 1-1/2" face width inverted "T" bar ceilings.

Benefits

- Limits the passage of particle matter through the frame
- Allows relamping and servicing from below the ceiling

Features

- Meets federal standard for class 100,000, 10,000, and 1,000
- Gasketed housing
- Hinge and latch extruded aluminum door

Application

- Office
- Banks
- Hospitality
- Petrol and Convenience
- Fashion
- Cleanrooms
- Food Processing

DCL Designer Cleanroom

Versions

