



BRM800 - excellent performance, superior durability

Dome Top Bollard BRM800

A cousin to its' louvered relative, the BRM800 dome top bollard typifies the construction detailing that is evident throughout the line. Silicone seals and gaskets at all points of material transition assure weather-tight seals, lamp chambers are free from insects and dirt, and the luminaires will provide years of trouble free service.

Benefits

- Uniform illumination
- Wide spacings
- Remarkable brightness control
- Ensures lasting performance in harsh conditions
- Fade and abrasion resistant

Features

- Rugged aluminum construction
- Anodized die formed aluminum reflector
- Hammertone reflector
- Polyester powdercoat finish

Application

- Landscape
- Walkways
- Parks and Plazas

Dome Top Bollard BRM800

Versions

