



DPWL Designer Wet Location – Superior and practical

DPWL Designer Wet Location

Designer Wet Location is a recessed luminaire UL Listed for damp and wet locations (for covered ceiling use only).

Benefits

- Limits the passage of particle matter through the frame
- Allows relamping and servicing from below the ceiling

Features

- Gasketed housing
- Suitable for wet locations

Application

- Office
- Banks
- Hospitality
- Petrol and Convenience
- Fashion
- Cleanrooms
- Food Processing

DPWL Designer Wet Location

Versions

