



# DWL1 - adding safe and guiding light to your space

## DWL1 Beacon

The DWL1 is a low voltage beacon constructed of a single-piece compression molded fiberglass reinforced polyester composite lower housing and die cast brass upper housing. The natural brass is as-cast and tumble polished. Composite is pressure formed, molded-in color. Optical assembly includes a borosilicate glass.

### Benefits

- Superior durability
- UV and corrosion resistant
- Protected against moisture, dust and insects
- Suitable for a variety of applications

### Features

- Reinforced polyester composite
- Silicone gasketing
- Lamp included

### Application

- Walkway