



# ECH - Highly durable and efficient

## ECH Linear Pole Mount

A highly durable and efficient exterior pole mounted fixture designed to maximize light distribution and withstand the harshest of conditions. Applications include roadways, parking lots, retail exteriors, perimeter lighting, loading areas, tunnels and other wet and/or dusty locations. The ECH's radius drop lens allows for optimal light output and superior distribution.

### Benefits

- Designed to be durable and weather resistant
- Optimal light output and superior distribution

### Features

- Housing is brake formed from heavy gauge aluminum
- The one piece reflector is removable without the use of tools
- The standard ECH lens is an impact resistant, lineally ribbed DR Acrylic

### Application

- Security Lighting
- Parks and Plazas
- Road and Street

# ECH Linear Pole Mount

## Versions

