



Deliver more than expected

EcoForm LED site and area G2 - small (ECF-S)

In any outdoor site and area project, the next generation of Gardco EcoForm LED site and area luminaires are more than sources of illumination they offer the best of all worlds: saving energy, saving time, and saving money for significant and enduring value. It's not just about meeting technical requirements. It's about looking out for the best interests of your customers, and going the extra mile to uncover new savings and conveniences!

Benefits

- A heightened sense of security by incorporating lumen outputs from 6,000-42,000
- Maintain consistent aesthetics throughout the site with two housing sizes
- A variety of mounting options available for new installs and retrofit applications including retrofit mounting styles
- Deliver optimum light levels without over- or under- lighting with true 400W and 1000W HID equivalency
- Enhanced long-term energy savings and personalized functionality with a full range of outdoor lighting controls

Features

- Type 2, 3, 4, 5, 5 Wide, and Auto Front Row distributions available with optional factory pre-aimed rotation at 90° or 270°
- Two housing sizes available with 2, 3, 4, 5 or 6 LED modules
- Standard arm mount, retrofit arm mount, slipfitter mount and wall mount available
- Stylized, one piece die-cast aluminum housing with built in heat sink
- IP66 rated optical assembly and IP65 rated electrical housing

Application

- Security Lighting
- Area Lighting
- Site Lighting

EcoForm LED site and area G2 - small (ECF-S)

Versions




Accessories




Ordercode Prog MR



Ordercode Prog MR Rem



Ordercode Prog MR Optics



Ordercode SiteWise

