



Consistent visual comfort

Evolution MR16 4 1/2"

Energy efficient frames designed for residential applications, CSA certified for direct contact with insulation. For installation in plaster or drywall ceilings up to 1" thick. luminaires come complete with swivel locking mounting bars for easy installation.

Benefits

- 50° physical and reflected cut off
- Precision optics minimize aperture brightness
- Unitized optics ensure consistent performance

Features

- 50° physical and reflected cut off
- Precision optics minimize aperture brightness
- Unitized optics ensure consistent performance

Application

- Residential
- Office
- Banks
- Hospitality
- Airports
- Fashion

Evolution MR16 4 1/2"

Versions

