



# FBD – Basic, yet versatile

## FBD High Bay

The FBD Fluorescent High Bay is a flexible luminaire designed to meet the needs of today's industrial environment. This luminaire is available with T5HO or T8 lamps. The 95% reflective specular aluminum reflectors and solid body design result in a sturdy and efficient luminaire. A variety of mounting methods and accessories allow the luminaire to be used in many different types of applications.

### Benefits

- Long lasting, durable finish
- Excellent optical control
- Easy maintenance
- Multiple mounting methods

### Features

- Steel housing with white polyester powder finish
- Specular aluminum reflectors
- Toolless entry
- Chain or cable hanging

### Application

- Manufacturing
- Industrial
- Warehouse

## FBD High Bay

### Versions

