



# FBF Industrial - Flexible and efficient

## FBF High Bay

The FBF Fluorescent High Bay is a flexible luminaire designed to meet the needs of today's industrial environment. This luminaire is available with T5HO or T8 lamps. The 95% reflective specular aluminum reflectors and solid body design result in a sturdy and efficient luminaire. A variety of mounting methods and accessories allow the luminaire to be used in many different types of applications.

### Benefits

- Efficient lighting

### Features

- Steel housing with white polyester powder finish

### Application

- Manufacturing
- Industrial
- Warehouse