



FBF Industrial - Flexible and efficient

FBF High Bay

The FBF Fluorescent High Bay is a flexible luminaire designed to meet the needs of today's industrial environment. This luminaire is available with T5HO or T8 lamps. The 95% reflective specular aluminum reflectors and solid body design result in a sturdy and efficient luminaire. A variety of mounting methods and accessories allow the luminaire to be used in many different types of applications.

Benefits

- Efficient lighting

Features

- Steel housing with white polyester powder finish

Application

- Manufacturing
- Industrial
- Warehouse

FBF High Bay

Versions

