



FluxStream – simple, easy, convenient

FluxStream LED Industrial

The FluxStream family of LED linear luminaires deliver high-quality, more uniform light versus fluorescents for a greater range of applications. Choose FluxStream for simple, robust LED light industrial commercial linear lighting solutions that need to perform and endure.

Benefits

- Simple form
- Convenient specification
- Ease of installation
- Ease of maintenance

Features

- Delivers up to 134 LPW
- Multiple CCT and lumen options
- Standard 0-10V dimming
- Multiple mounting methods

Application

- Office
- Banks
- Hospitality
- Manufacturing
- Education

FluxStream LED Industrial

Versions



FSI440L840-UNV-DIM

