



G Series - Efficient and economical

G Series High Bay

A high efficiency fluorescent high-bay that provides exceptional light distribution for general areas. Applications include warehouses, manufacturing facilities, open construction retail and gymnasiums with the wire guard safety option. This new and unique design adds another beneficial feature to this fixture series. The hinged socket bracket assembly pivots down with a quick release, allowing for immediate access to all internal fixture components.

Benefits

- Rigid housing construction
- Quick and easy access to internal components
- Excellent light distribution
- Fits many applications

Features

- Brake formed housing from heavy gauge cold rolled steel
- Hinged socket bar assembly
- Highly specular aluminum reflector
- Flexible mounting methods

Application

- Manufacturing
- Industrial
- Warehouse
- Retail

G Series High Bay

Versions

