



GP Flood - versatility with scale

GP Flood Series - GP2

The GP2 Flood Series combines architectural design with on-site versatility and is designed for general purpose floodlighting installations. Applications include security, roadway, area, accent, facade, recreational fields, flagpole, and sign lighting. The GP2 Flood series is available with ED17 lamps for pulse start metal halide and B17 lamps for high pressure sodium up to 175 watts. Reflectors include general purpose, spot and cut-off optics for control of light trespass. IP65 Rated for extra protection against water, dust and debris, and can be aimed above or below horizontal. The LED version is available in 30 LEDs in either 40W or 60W configurations.

Benefits

- Suitable for a variety of applications
- Ensures cool operation
- Durable and reliable construction
- Quick and easy maintenance
- Ensures lasting performance in harsh environmental conditions

Features

- Offers a variety of optical distributions
- Integral heat sink
- Die cast aluminum housing
- Hinged lens
- IP65 rating

GP Flood Series - GP2

Application

- Arena and Sports
- Bridges, Monuments, Facades
- Security Lighting
- Sign Lighting
- Walkways

Versions

