



GXN Series - Aesthetic and efficient

GXN Series High Bay

A high efficiency fluorescent high-bay that provides exceptional light distribution for general areas, in a narrow profile housing. Applications include warehouses, manufacturing facilities, open construction retail and gymnasiums with the wireguard safety option.

Benefits

- Sturdy and rigid luminaire
- Good optical performance
- Fits many applications

Features

- Heavy gauge cold rolled steel housing
- Precision aluminum reflector
- High efficiency prismatic lens standard
- Multiple mounting methods

Application

- Manufacturing
- Industrial
- Retail

GXN Series High Bay

Versions

